




Basic Pad

Flat Type with Ribs

ZP Series

How to Order



Dimensions/ Models	Construction	Mounting Bracket Assembly
p. 51	p. 117	From p. 121

From p. 51	p. 117	From p. 121
------------	--------	-------------

From p. 57	p. 118	From p. 124
------------	--------	-------------

① Adapter (Lock ring) material

Nil	Brass
S*1	Stainless steel (Stainless steel 304)

*1 Only applicable to the pad unit (with lock ring) and the pad with adapter (Vacuum inlet direction: Vertical (Option "T"))

② Vacuum inlet direction

Nil	Pad unit
T	Vertical
R	Lateral (With One-touch fitting)
Y	Lateral (With barb fitting)

③ Pad diameter

10	ø10
13	ø13
16	ø16
20	ø20
25	ø25
32	ø32
40	ø40
50	ø50

④ Material

N	NBR
S	Silicone rubber*1 *2
U	Urethane rubber
F	FKM
GN	Conductive NBR
GS	Conductive silicone rubber

*1 Uses a material compliant with a dissolution test of the FDA (U.S. Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use."

*2 Uses a material compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Japanese Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Japan Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Japanese Ministry of Health and Welfare Notification No. 370, 1959)

⑤ Buffer specification

J	Rotating
K	Non-rotating

⑥ Buffer stroke

Stroke [mm]	Pad diameter [mm]							
	ø10	ø13	ø16	ø20	ø25	ø32	ø40	ø50
10	●	●	●	●	●	●	●	●
20	●	●	●	●	●	●	●	●
30	●	●	●	●	●	●	●	●
40	●	●	●	●	●	●	—	—
50	●	●	●	●	●	●	●	●

With adapter

⑦ Vacuum inlet

○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter [mm]		
			ø10 to ø16	ø20 to ø32	ø40, ø50
Male thread	AS5	M5 x 0.8	○*4	○*4	—
	AS6	M6 x 1	○*4	○*4	○*4
	AG01	G1/8	○*4	○*4	—
	AG02	G1/4	—	—	○*4
Female thread	Nil	M3 x 0.5	○ (Connection thread: A5/A6)	○ (Connection thread: A6)	○ (Connection thread: A6)
		M5 x 0.8	—	○ (Connection thread: A8)	○ (Connection thread: A8)
	B5	M5 x 0.8	○*4	○*4	—
	B6	M6 x 1	○*4	○*4	○*4
	B8	M8 x 1.25	—	○*4	○*4
	BG01	G1/8	○*4	○*4	—
	BG02	G1/4	—	—	○*4
	B01	Rc1/8	○*4	○*4	○*4
	N01 *3	NPT1/8	○*4	○*4	○*4
	T01 *3	NPT1/8	○*4	○*4	○*4
One-touch fitting	04	ø4	●	●	—
	06	ø6	●	●	●
	08	ø8	—	●	●
Barb fitting	N4	For ø4 nylon tubing*1	△	△	—
	N6	For ø6 nylon tubing*1	△	△	△
	U4	For ø4 soft tubing*2	△	△	—
	U6	For ø6 soft tubing*2	△	△	△

*1 Nylon tube piping *2 Soft nylon/Polyurethane tube piping

*3 Not compatible with stainless steel materials *4 Use the connection thread.

⑧ Connection thread

○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter [mm]		
			ø10 to ø16	ø20 to ø32	ø40, ø50
Male thread*1	A5	M5 x 0.8	○*2△	—	—
	A6	M6 x 1	○*2△	○*2●△	○*2●△
	A8	M8 x 1	—	○*2●△	○*2●△
Female thread	B5	M5 x 0.8	●△	●△	—
	B6	M6 x 1	●△	●△	●△
	B8	M8 x 1.25	—	●△	●△

*1 The mounting nut is shipped together with the product (unassembled). *2 ○: ZPT/Vertical comes with a vacuum inlet (female thread).

With buffer

⑦ Vacuum inlet

○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter [mm]		
			ø10 to ø16	ø20 to ø32	ø40, ø50
Female thread	B5	M5 x 0.8	○	○	○
	B01	Rc1/8	—	—	○
	N01	NPT1/8	—	—	○
	T01	NPT1/8	—	—	○
One-touch fitting	04	ø4	○●	○●	—
	06	ø6	○●	○●	○●
	08	ø8	—	●	○●
Barb fitting	N4	For ø4 nylon tubing*1	△	△	—
	N6	For ø6 nylon tubing*1	○△	○△	○△
	U4	For ø4 soft tubing*2	△	△	—
	U6	For ø6 soft tubing*2	○△	○△	○△

*1 Nylon tube piping

*2 Soft nylon/Polyurethane tube piping

⑧ Connection thread

○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter [mm]		
			ø10 to ø16	ø20 to ø32	ø40, ø50
Male thread*1	A10	M10 x 1	○●△	○●△	—
	A14	M14 x 1	—	—	○●△

*1 The mounting nut and ○: ZPT/Vertical buffer are shipped together with the product (unassembled).

⑨ Lock ring

Symbol	Pad diameter
Nil	All sizes
X19	Without lock ring

Lock ring unit

Part no.	Pad diameter [mm]
ZP□L1	ø10 to ø16
ZP□L2	ø20 to ø32
ZP□L3	ø40, ø50

□: Nil/Brass S/Stainless steel

* The pad unit lock ring is shipped together with the product (unassembled).

Model
Selection

ZP
Basic

Flat Type

Flat Type
with Ribs

Flat,
Ball Joint Type

Belows Type

Thin Flat Type

Thin Flat Type
with Ribs

Deep Type

Construction

Mounting
Bracket
Assembly

Precautions



How to Order

Dimensions/ Models	Construction	Mounting Bracket Assembly
p. 62	p. 119	From p. 127

Pad unit	ZP	10 F N		p. 62	p. 119	From p. 127
* Pad unit's sales unit: 10 pcs. (Pad diameter: ø20 mm or less only)						
With adapter	ZP T	10 F N - B5 - A8		From p. 62	p. 119	From p. 127
With buffer	ZP T	10 F N J 10 - B5 - A10		From p. 65	p. 120	From p. 129

● Ball joint type

1 Vacuum inlet direction

T	Vertical
R	Lateral (With One-touch fitting)

2 Pad diameter

10	ø10
13	ø13
16	ø16
20	ø20
25	ø25
32	ø32
40	ø40
50	ø50

5 Buffer stroke

Stroke [mm]	Pad diameter [mm]	
	ø10 to ø16	ø20 to ø50
10	●	●
20	●	●
30	●	●
40	●	—
50	●	●

3 Material

N	NBR
S	Silicone rubber*1 *2
U	Urethane rubber
F	FKM
GN	Conductive NBR
GS	Conductive silicone rubber

4 Buffer specification

J	Rotating
K	Non-rotating

*1 Uses a material compliant with a dissolution test of the FDA (U.S. Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use."

*2 Uses a material compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Japanese Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Japan Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Japanese Ministry of Health and Welfare Notification No. 370, 1959)

With adapter

⑥ Vacuum inlet/⑦ Connection thread

○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting)

⑥ Vacuum inlet			⑦ Connection thread			Pad diameter [mm]		
Type	Symbol	Size	Type	Symbol	Size	ø10 to ø16	ø20 to ø32	ø40, ø50
Female thread	B5	M5 x 0.8	Male thread	A8	M8 x 1	○	—	—
				A10	M10 x 1	—	○	—
				A14	M14 x 1	—	—	○
—	Nil	—※1	Female thread	B5	M5 x 0.8	○	○	—
				B8	M8 x 1.25	—	○	○
				B01	Rc1/8	—	○	○
				N01	NPT1/8	—	○	○
				T01	NPTF1/8	—	○	○
				B5	M5 x 0.8	●	—	—
One-touch fitting	04	ø4	Female thread	B5	M5 x 0.8	●	●	●
	06	ø6		B8	M8 x 1.25	—	●	●
	08	ø8		B5	M5 x 0.8	—	●	●
				B8	M8 x 1.25	—	●	●

*1 Use the connection thread.

With buffer

6 Vacuum inlet

○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting)

Type	Symbol	Size	Pad diameter [mm]		
			ø10 to ø16	ø20 to ø32	ø40, ø50
Female thread	B5	M5 x 0.8	○	—	—
	B01	Rc1/8	—	—	○
	N01	NPT1/8	—	○	○
	T01	NPTF1/8	—	○	○
One-touch fitting	04	ø4	○●	—	—
	06	ø6	○●	○●	○●
	08	ø8	—	○●	○●

7 Connection thread ○: ZPT/Vertical ●: ZPR/Lateral

Pad diameter [mm]

Type	Symbol	Size	Pad diameter [mm]		
			ø10 to ø16	ø20 to ø32	ø40, ø50
Male thread	A10	M10 x 1		—	—
	A14	M14 x 1	—		

Lock ring unit

Part no.	Pad diameter [mm]
ZPLF	ø40, ø50



* The following parts are shipped together with the product (unassembled).

- Mounting nut for the types with an adapter or a buffer
- Buffer for the type with a buffer (Vacuum inlet: Vertical)



Basic Pad Bellows Type ZP Series

How to Order



Dimensions/ Models	Construction	Mounting Bracket Assembly
p. 68	p. 115 p. 117	From p. 121
From p. 69	p. 115 p. 117	From p. 121
From p. 79	p. 116 p. 118	From p. 124

① Adapter (Lock ring) material

Nil	Brass
S*1	Stainless steel (Stainless steel 304)

*1 Only applicable to the pad unit (with lock ring) and the pad with adapter (Vacuum inlet direction: Vertical (Option "T"))

② Vacuum inlet direction

Nil	Pad unit
T	Vertical
R	Lateral (With One-touch fitting)
Y	Lateral (With barb fitting)

③ Pad diameter

06	ø6	20	ø20
08	ø8	25	ø25
10	ø10	32	ø32
13	ø13	40	ø40
16	ø16	50	ø50

④ Material

N	NBR
S	Silicone rubber*1 *2
U	Urethane rubber
F	FKM
GN	Conductive NBR
GS	Conductive silicone rubber

*1 Uses a material compliant with a dissolution test of the FDA (U.S. Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use."

*2 Uses a material compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Japanese Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Japan Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Japanese Ministry of Health and Welfare Notification No. 370, 1959)

⑤ Buffer specification

J	Rotating
K	Non-rotating
JN*1	Rotating (Without buffer plate)
KN*1	Non-rotating (Without buffer plate)

*1 Only for pad diameters ø6 and ø8

⑥ Buffer stroke

Stroke [mm]	Pad diameter [mm]									
	ø6	ø8	ø10	ø13	ø16	ø20	ø25	ø32	ø40	ø50
6	●	●	—	—	—	—	—	—	—	—
10	●	●	●	●	●	●	●	●	●	●
15	●	●	—	—	—	—	—	—	—	—
20	—	—	●	●	●	●	●	●	●	●
25	●	●	—	—	—	—	—	—	—	—
30	—	—	●	●	●	●	●	●	●	●
40	—	—	●	●	●	●	●	●	—	—
50	—	—	●	●	●	●	●	●	●	●

With adapter

⑦ Vacuum inlet ○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter [mm]				
			ø6, ø8	ø10 to ø16	ø20 to ø32	ø40, ø50	
Male thread	A5	M5 x 0.8	○*1	—	—	—	
	AS5	M5 x 0.8	○*1	○*1	○*1	—	
	A6	M6 x 1	○*1	—	—	—	
	AS6	M6 x 1	—	○*1	○*1	○*1	
	AG01	G1/8	—	○*1	○*1	—	
Female thread	AG02	G1/4	—	—	—	○*1	
	Nil	M3 x 0.5	—	○ (Connection thread: AS/AG)	○ (Connection thread: AG)	○ (Connection thread: AG)	
	Nil	M5 x 0.8	—	—	○ (Connection thread: AG)	○ (Connection thread: AG)	
	B4	M4 x 0.7	○*1	—	—	—	
	B5	M5 x 0.8	○*1	○*1	○*1	—	
	B6	M6 x 1	—	○*1	○*1	○*1	
	B8	M8 x 1.25	—	—	○*1	○*1	
	BG01	G1/8	—	○*1	○*1	—	
	BG02	G1/4	—	—	—	○*1	
	B01	Rc1/8	—	○*1	○*1	○*1	
One-touch fitting	N01*4	NPT1/8	—	○*1	○*1	○*1	
	T01*4	NPTF1/8	—	○*1	○*1	○*1	
	04	ø4	●	●	●	—	
Barb fitting	06	ø6	●	●	●	●	
	08	ø8	—	—	●	●	
	N4	For ø4 nylon tubing*2	△	△	△	—	
	N6	For ø6 nylon tubing*2	△	△	△	△	
	U4	For ø4 soft tubing*3	△	△	△	—	
	U6	For ø6 soft tubing*3	△	△	△	△	

*1 Use the connection thread. *2 Nylon tube piping *3 Soft nylon/Polyurethane tube piping
*4 Not compatible with stainless steel materials

⑧ Connection thread ○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter [mm]				
			ø6, ø8	ø10 to ø16	ø20 to ø32	ø40, ø50	
Male thread*1	A5	M5 x 0.8	●△	○*2△	—	—	
	A6	M6 x 1	●△	○*2●△	○*2●△	○*2●△	
	A8	M8 x 1	—	—	○*2●△	○*2●△	
Female thread	B4	M4 x 0.7	●△	—	—	—	
	B5	M5 x 0.8	●△	●△	●△	—	
	B6	M6 x 1	—	●△	●△	●△	
	B8	M8 x 1.25	—	—	●△	●△	

*1 The mounting nut is shipped together with the product (unassembled). *2 ○: ZPT/Vertical comes with a vacuum inlet (female thread).

With buffer

⑦ Vacuum inlet ○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter [mm]				
			ø6, ø8	ø10 to ø16	ø20 to ø32	ø40, ø50	
Female thread	B3	M3 x 0.5	○	—	—	—	
	B5	M5 x 0.8	○	○	○	○	
	B01	Rc1/8	—	—	—	○	
	N01	NPT1/8	—	—	—	○	
One-touch fitting	T01	NPTF1/8	—	—	—	○	
	04	ø4	○●	○●	○●	—	
	06	ø6	○●	○●	○●	○●	
Barb fitting	08	ø8	—	—	●	○●	
	N4	For ø4 nylon tubing*1	○△	△	△	—	
	N6	For ø6 nylon tubing*1	△	○△	○△	○△	
	U4	For ø4 soft tubing*2	○△	△	△	—	
	U6	For ø6 soft tubing*2	△	○△	○△	○△	

*1 Nylon tube piping *2 Soft nylon/Polyurethane tube piping

⑧ Connection thread ○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter [mm]				
			ø6, ø8	ø10 to ø16	ø20 to ø32	ø40, ø50	
Male thread*1	A8	M8 x 1	○●△	—	—	—	
	A10	M10 x 1	—	○●△	○●△	—	
	A14	M14 x 1	—	—	—	○●△	

*1 The mounting nut, buffer plate, and ○: ZPT/Vertical buffer are shipped together with the product (unassembled).

⑨ Lock ring

Symbol	Pad diameter [mm]	
Nil	ø6, ø8	ø10 to ø50
X19	None*1	With lock ring Without lock ring

*1 The lock ring cannot be used for pad diameters ø6 and ø8.

Lock ring unit

Part no.	Pad diameter [mm]
ZP□L1	ø10 to ø16
ZP□L2	ø20 to ø32
ZP□L3	ø40, ø50

□: Nil/Brass S/Stainless steel

* The pad unit lock ring is shipped together with the product (unassembled).



Basic Pad

Thin Flat Type

ZP Series




How to Order

Pad unit ZP

* Pad unit's sales unit: 10 pcs.

With adapter ZP

With buffer ZP



Dimensions/ Models	Construction	Mounting Bracket Assembly
p. 87	p. 115	From p. 121

From p. 87	p. 115	From p. 121
------------	--------	-------------

From p. 92	p. 116	From p. 124
------------	--------	-------------

1 Adapter material

Nil	Brass
S*1	Stainless steel (Stainless steel 304)

*1 Only applicable to the pad with adapter (Vacuum inlet direction: Vertical (Option "T"))

2 Vacuum inlet direction

Nil	Pad unit
T	Vertical
R	Lateral (With One-touch fitting)
Y	Lateral (With barb fitting)

3 Pad diameter

10	ø10
13	ø13
16	ø16

4 Material

N	NBR
S	Silicone rubber *1 *2
U	Urethane rubber
F	FKM
GN	Conductive NBR
GS	Conductive silicone rubber

*1 Uses a material compliant with a dissolution test of the FDA (U.S. Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use."

*2 Uses a material compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Japanese Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Japan Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Japanese Ministry of Health and Welfare Notification No. 370, 1959)

5 Buffer specification

J	Rotating
K	Non-rotating
JN	Rotating (Without buffer plate)
KN	Non-rotating (Without buffer plate)

6 Buffer stroke

Stroke [mm]	Pad diameter All sizes
6	●
10	●
15	●
25	●

With adapter

7 Vacuum inlet

○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter All sizes
Male thread	A5	M5 x 0.8	○
	A6	M6 x 1	○
Female thread	B4	M4 x 0.7	○
	B5	M5 x 0.8	○
One-touch fitting	04	ø4	●
	06	ø6	●
Barb fitting	N4	For ø4 nylon tubing	△
	N6	For ø6 nylon tubing	△
	U4	For ø4 soft tubing	△
	U6	For ø6 soft tubing	△

8 Connection thread ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter All sizes
Male thread*1	A5	M5 x 0.8	●△
	A6	M6 x 1	●△
Female thread	B4	M4 x 0.7	●△
	B5	M5 x 0.8	●△

It is not necessary to select a connection thread for ○: ZPT/Vertical. Use the vacuum inlet.

*1 The mounting nut is shipped together with the product (unassembled).

With buffer

7 Vacuum inlet

○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter All sizes
Female thread	B3	M3 x 0.5	○
	B5	M5 x 0.8	○
One-touch fitting	04	ø4	○●
	06	ø6	○●
Barb fitting	N4	For ø4 nylon tubing*1	○△
	N6	For ø6 nylon tubing*1	△
	U4	For ø4 soft tubing*2	○△
	U6	For ø6 soft tubing*2	△

*1 Nylon tube piping

*2 Soft nylon/Polyurethane tube piping

8 Connection thread

○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter All sizes
Male thread*1	A8	M8 x 1	○●△

*1 The mounting nut, buffer plate, and ○: ZPT/Vertical buffer are shipped together with the product (unassembled).

Model
Selection

ZP
Basic

Flat Type

Flat Type
with Ribs

Flat,
Ball Joint Type

Bellows Type

Thin Flat Type

Thin Flat Type
with Ribs

Deep Type

Construction

Mounting
Bracket
Assembly

Precautions



Pad unit ZP 10 CT N p. 96 p. 115 From p. 121

* Pad unit's sales unit: 10 pcs.

With adapter ZP [] T 10 CT N - A5 - [] From p. 96 p. 115 From p. 121

With buffer ZP [] T 10 CT N J 6 - B3 - A8 From p. 101 p. 116 From p. 124

1 2 3 4 5 6 7 8

*1 The mounting nut, buffer plate, and ○: ZPT/Vertical buffer are shipped together with the product (unassembled).




Basic Pad

Deep Type

ZP Series



How to Order



① Adapter (Lock ring) material

Nil	Brass
S*1	Stainless steel (Stainless steel 304)

*1 Only applicable to the pad unit (with lock ring) and the pad with adapter (Vacuum inlet direction: Vertical (Option "T"))

② Vacuum inlet direction

Nil	Pad unit
T	Vertical
R	Lateral (With One-touch fitting)
Y	Lateral (With barb fitting)

③ Pad diameter

10	ø10
16	ø16
25	ø25
40	ø40

④ Material

N	NBR
S	Silicone rubber*1 *2
U	Urethane rubber
F	FKM
GN	Conductive NBR
GS	Conductive silicone rubber

*1 Uses a material compliant with a dissolution test of the FDA (U.S. Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use."

*2 Uses a material compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Japanese Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Japan Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Japanese Ministry of Health and Welfare Notification No. 370, 1959)

⑤ Buffer specification

J	Rotating
K	Non-rotating

⑥ Buffer stroke

Stroke [mm]	Pad diameter [mm]			
	ø10	ø16	ø25	ø40
10	●	●	●	●
20	●	●	●	●
30	●	●	●	●
40	●	●	●	—
50	●	●	●	●

With adapter

⑦ Vacuum inlet

○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter [mm]			
			ø10, ø16	ø25	ø40	
Male thread	AS5	M5 x 0.8	○*4	○*4	—	
	AS6	M6 x 1	○*4	○*4	○*4	
	AG01	G1/8	○*4	○*4	—	
	AG02	G1/4	—	—	○*4	
Female thread	Nil	M3 x 0.5	○ (Connection thread: A5/A6)	○ (Connection thread: A6)	○ (Connection thread: A6)	
		M5 x 0.8	—	○ (Connection thread: A8)	○ (Connection thread: A8)	
	B5	M5 x 0.8	○*4	○*4	—	
	B6	M6 x 1	○*4	○*4	○*4	
	B8	M8 x 1.25	—	○*4	○*4	
	BG01	G1/8	○*4	○*4	—	
	BG02	G1/4	—	—	○*4	
	B01	Rc1/8	○*4	○*4	○*4	
	N01*3	NPT1/8	○*4	○*4	○*4	
	T01*3	NPTF1/8	○*4	○*4	○*4	
One-touch fitting	04	ø4	●	●	—	
	06	ø6	●	●	●	
	08	ø8	—	●	●	
Barb fitting	N4	For ø4 nylon tubing*1	△	△	—	
	N6	For ø6 nylon tubing*1	△	△	△	
	U4	For ø4 soft tubing*2	△	△	—	
	U6	For ø6 soft tubing*2	△	△	△	

*1 Nylon tube piping *2 Soft nylon/Polyurethane tube piping

*3 Not compatible with stainless steel materials *4 Use the connection thread.

⑧ Connection thread ○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter [mm]			
			ø10, ø16	ø25	ø40	
Male thread*1	A5	M5 x 0.8	○*2 △	—	—	
	A6	M6 x 1	○*2 ● △	○*2 △	○*2 △	
	A8	M8 x 1	—	○*2 △	○*2 △	
	B5	M5 x 0.8	● △	● △	—	
Female thread	B6	M6 x 1	● △	● △	● △	
	B8	M8 x 1.25	—	● △	● △	

*1 The mounting nut is shipped together with the product (unassembled).

*2 ○: ZPT/Vertical comes with a vacuum inlet (female thread).

With buffer

⑦ Vacuum inlet

○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter [mm]			
			ø10, ø16	ø25	ø40	
Female thread	B5	M5 x 0.8	○	○	○	
	B01	Rc1/8	—	—	○	
	N01	NPT1/8	—	—	○	
	T01	NPTF1/8	—	—	○	
One-touch fitting	04	ø4	○ ●	○ ●	—	
	06	ø6	○ ●	○ ●	○ ●	
	08	ø8	—	●	○ ●	
Barb fitting	N4	For ø4 nylon tubing*1	△	△	—	
	N6	For ø6 nylon tubing*1	○ △	○ △	○ △	
	U4	For ø4 soft tubing*2	△	△	—	
	U6	For ø6 soft tubing*2	○ △	○ △	○ △	

*1 Nylon tube piping

*2 Soft nylon/Polyurethane tube piping

⑧ Connection thread ○: ZPT/Vertical ●: ZPR/Lateral (With One-touch fitting) △: ZPY/Lateral (With barb fitting)

Type	Symbol	Size	Pad diameter [mm]			
			ø10, ø16	ø25	ø40	
Male thread*1	A10	M10 x 1	○ ● △	○ ● △	—	
	A14	M14 x 1	—	—	○ ● △	

*1 The mounting nut and ○: ZPT/Vertical buffer are shipped together with the product (unassembled).

⑨ Lock ring

Symbol	Pad diameter
	All sizes
Nil	With lock ring
X19	Without lock ring

Lock ring unit

Part no.	Pad diameter [mm]
ZP□L1	ø10, ø16
ZP□L2	ø25
ZP□L3	ø40

□: Nil/Brass S/Stainless steel

* The pad unit lock ring is shipped together with the product (unassembled).

Model
Selection

ZP
Basic

Flat Type

Flat Type
with Ribs

Flat,
Ball Joint Type

Bellows Type

Thin Flat Type

Thin Flat Type
with Ribs

Deep Type

Construction

Mounting
Bracket
Assembly

Precautions